Insulated Tool Kits

General-Purpose Insulated 22-Piece Tool Kit

- Case includes three pallets with customfitted pockets for each tool, piano-hinged cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items.
- Inside dimensions: 7-3/4" W x 14-1/4" D x 8" H (451 mm x 362 mm x 203 mm).
- Overall dimensions: 18-7/8" W x 15-3/8" D x 8-1/4" H (479 mm x 391 mm x 210 mm).
- Replacement case (Cat. No. 33537) available.

See individual tool listings for more details.



33527

Cat. No.	Kit Contains		Weight
33527			24.30 lbs. (11 kg)
	Cat. No.	Description	
	D2000-9NE-INS	insulated side-cutting pliers	
	12098-INS	insulated universal side-cutting pliers	
	D2000-28-INS	insulated diagonal-cutting pliers	
	D2000-48-INS	insulated diagonal-cutting pliers – angled head	
	D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
	D220-7-INS	insulated diagonal-cutting pliers – tapered nose	
	D203-6-INS	insulated long-nose pliers – side-cutting	
	D203-7-INS	insulated long-nose pliers – side-cutting	
	601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
	601-7-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 7")	
	612-4-INS	insulated cabinet-tip – round-shank screwdriver (1/8" x 4")	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
	602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
	633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	
	603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
	633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")	
	D502-10-INS	insulated pump pliers	
	11045-INS	insulated wire stripper/cutter	
	63050-INS	insulated high-leverage cable cutter	
	1571-INS	insulated lineman's skinning knife	
	1005-INS	insulated crimping/cutting tool	
	33537	extra-sturdy, bright-yellow case	

All dimensions are in inches and (millimeters).

AWARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

AWARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

AWARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

AWARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.





81

Insulated Tool Kits

∲ 1000 V

Utility Insulated 13-Piece Tool Kit

- The custom case includes two pallets with custom-fitted pockets for each tool, piano-hinged case cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items.
- Inside dimensions: 17-3/4" W x 14-1/4" D x 8" H (451 mm x 362 mm x 203 mm).
- Overall dimensions: 18-7/8" W x 15-3/8" D x 8-1/4" H (479 mm x 391 mm x 210 mm).
- Replacement case (Cat. No. 33535) available.

Cat. No. Kit Contains

33525



Cat. No.	Description			
D2000-9NE-INS	insulated side-cutting pliers			
D2000-28-INS	insulated diagonal-cutting pliers		Cat. No.	
D2000-48-INS	insulated diagonal-cutting pliers – angled head		603-4-INS	i
D203-8-INS	insulated heavy-duty long-nose pliers – side-cutting			r
602-4-INS	insulated cabinet-tip –		633-7-INS	i
	round-shank screwdriver (1/4" x 4")			1
602-7-INS	insulated cabinet-tip –		63050-INS	i
	round-shank screwdriver (5/16" x 7")		D502-10-INS	i
602-8-INS	insulated cabinet-tip –		1571-INS	i
	round-shank screwdriver (3/8" x 8")	-	33535	6
633-4-INS	insulated Phillips-tip –			
	round-shank screwdriver (#1 x 4")			

Weight

20.05 lbs. (9 kg)

Utility Insulated 13-Piece Tool Kit

- The light, compact, soft roll-up carry case provides ٠
 - protective storage with custom-fitted pockets for each tool.
- Kit includes a padded, adjustable shoulder strap. Case dimensions:
 - Opened 24-1/2" x 24-1/2" (622 mm x 622 mm). Closed 24-1/2" x 5-1/2" (622 mm x 140 mm).
- Replacement roll-up case (Cat. No. 33535SC) available.

Cat. No.	Kit Contains		Weight
33525SC			9.75 lbs. (4.4 kg)
	Cat. No.	Description	
	D2000-9NE-INS	insulated side-cutting pliers	
	D2000-28-INS	insulated diagonal-cutting pliers	
	D2000-48-INS	insulated diagonal-cutting pliers – angled head	
	D203-8-INS	insulated heavy-duty long-nose pliers - side-cutting	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
	602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
	633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	

All dimensions are in inches and (millimeters).

AWARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source. 1000 V

AWARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel





Cat. No.	Description
603-4-INS	insulated Phillips-tip –
	round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip –
	round-shank screwdriver (#3 x 7")
63050-INS	insulated high-leverage cable cutter
D502-10-INS	insulated pump pliers
1571-INS	insulated lineman's skinning knife
33535SC	roll-up soft case with shoulder strap

AWARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

AWARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

AWARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

82

Insulated Tool Kits

Insulated 8-Piece Tool Kits

- Highly durable, black nylon case features: coil-zipper closure, polypropylene handles, custom-fitted tool pockets.
- Overall case dimensions are: 15-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm).
- Replacement case (Cat. No. 33536) available.

See individual tool listings for more details.

Premium Insulated 8-Piece Tool Kit

Cat. No.	Kit Contains		Woight
Gal. NU.	KIL GUIITAIIIS		Weight
33529			6.90 lbs. (3
	Cat. No.	Description	
	D2000-9NE-INS	insulated side-cutting pliers	_
	D2000-48-INS	insulated diagonal-cutting pliers	
	D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
	601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
	63050-INS	insulated high-leverage cable cutter	
	11055-INS	insulated wire stripper/cutter	
	33536	heavy-duty polyester case	

Basic Insulated 8-Piece Tool Kit

Cat. No.	Kit Contains		Weight
33526			6.90 lbs. (3 kg)
	Cat. No.	Description	
	D213-9NE-INS	insulated side-cutting pliers	
	D228-8-INS	insulated diagonal-cutting pliers	
	D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
	601-4-INS	insulated cabinet-tip - round-shank screwdriver (3/16" x 4")	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
	63050-INS	insulated high-leverage cable cutter	
	11045-INS	insulated wire stripper/cutter	
	33536	heavy-duty polyester case	

All dimensions are in inches and (millimeters).

AWARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

AWARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

AWARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

AWARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

83



\Lambda 1000 V

9-Piece Insulated Screwdriver Kit

- Nine-piece insulated screwdriver assortment with three sizes of each tip style: cabinet, keystone, and Phillips.
- Highly durable, black nylon case features: coil-zipper closure, polypropylene handles, custom-fitted tool pockets, extra pocket is provided for storage of papers or other items.
- Overall dimensions: 5-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm)
- Replacement case (Cat. No. 33538) available.

See individual tool listings for more details.

Ca 33

at. No.	Kit Contain	S	Weight	
3528			5.40 lbs.	(2.4
	Cat. No.	Description		
	601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")		
	601-7-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 7")		
	612-4-INS	insulated cabinet-tip – round-shank screwdriver (1/8" x 4")		
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")		
	602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")		
	602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")		
	633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")		
	603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")		
	633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")		
	33538	heavy-duty polyester case		



kg)

33528

Cushion-Grip Insulated 9-Piece Nut Driver Kits

- Nine-piece insulated nut driver assortment of popular sizes.
- Individually tested to exceed standards.
- Two layers of insulation provide protection against electric shock.
- Highly durable, black nylon case features: oil-zipper closure, polypropylene handles, custom-fitted tool pockets, extra pocket is provided for storage of papers or other items.
- Overall case dimensions are: 15" W x 12-3/4" L x 3-1/2" D (381 mm x 324 mm x 89 mm).
- Replacement case available Cat. No. 33534.

See individual tool listings for more details.

Cat. No.	Kit Contains		Weight
33524			6.00 lbs. (2.7 kg
	Cat. No.	Description	
	646-3/16-INS	insulated 3/16" hollow shaft nut driver, 6" shaft	
	646-1/4-INS	insulated 1/4" hollow shaft nut driver, 6" shaft	
	646-5/16-INS	insulated 5/16" hollow shaft nut driver, 6" shaft	
	646-11/32-INS	insulated 11/32" hollow shaft nut driver, 6" shaft	
	646-3/8-INS	insulated 3/8" hollow shaft nut driver, 6" shaft	
	646-7/16-INS	insulated 7/16" hollow shaft nut driver, 6" shaft	
	646-1/2-INS	insulated 1/2" hollow shaft nut driver, 6" shaft	
	646-9/16-INS	insulated 9/16" hollow shaft nut driver, 6" shaft	
	646-5/8-INS	insulated 5/8" hollow shaft nut driver, 6" shaft	
	33534	Custom heavy-duty Cordura® case	-

All dimensions are in inches and (millimeters).

AWARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source. 1000 V

AWARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel



Cordura[®] is a registered trademark of INVISTA for durable fabrics.

AWARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

AWARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

AWARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

