



Part No.	Size	T in [mm]	R in [mm]	W in [mm]	A in [mm]	B in [mm]	C in [mm]	D in [mm]
077818	2"	0.1 [3]	1.1 [29]	0.8 [20]	1.0 [25]	2.4 [60]	4.0 [102]	0.3 [7]
077819	2.5"	0.1 [3]	1.4 [37]	0.9 [23]	0.8 [20]	2.9 [74]	4.0 [102]	0.3 [7]
077820	3"	0.1 [3]	1.7 [43]	1.0 [26]	0.9 [23]	3.8 [96]	4.2 [107]	0.3 [8]
077821	3.5"	0.1 [3]	2.0 [50]	1.0 [26]	1.0 [26]	4.0 [101]	5.4 [137]	0.3 [8]
077822	4"	0.1 [3]	2.0 [52]	1.0 [26]	1.0 [26]	4.7 [120]	5.0 [127]	0.3 [8]
077823	6"	0.1 [3]	3.6 [92]	1.3 [32]	1.0 [27]	6.4 [163]	8.9 [226]	0.3 [8]
077824	5"	0.1 [3]	2.9 [74]	1.3 [32]	1.1 [29]	5.5 [139]	7.7 [196]	0.3 [8]

SIZES SHOWN ARE FOR REFERENCE 3D MODEL IS TO BE USED FOR MANUFACTURING / VERIFICATION		ALL CHANGES MUST BE APPROVED AND RECORDED BY ENGINEERING	
UNIT: INCHES UNLESS DUAL DIMENSION: INCH (METRIC)	PROJECTION 		
THIS DRAWING AND ALL TECHNICAL INFORMATION APPEARING HEREON ARE PROPERTY OF IPEX TECHNOLOGIES INC. AND MUST BE KEPT IN CONFIDENCE BY THE RECIPIENT. THE SAME MAY NOT BE USED OR REPRODUCED EITHER IN WHOLE OR IN PART WITHOUT THE EXPRESS CONSENT OF IPEX TECHNOLOGIES INC.		TITLE 2 HOLE PVC COATED STEEL PIPE STRAP	
PART APPEARANCE:	COLOR:	PAPER SIZE ANSI B	SCALE: 1:1
		DRAWN	DATE
		Z.LW	3/17/2018
SURFACE FINISHES: (UNLESS OTHERWISE NOTED)		APP'D	MAT'L:
INSIDE:		DIMENSIONS ARE IN INCHES TOLERANCES (UNLESS OTHERWISE SPECIFIED) FRACTIONAL ±3/32 DEC ±0.015 DEC ±0.030 DEC ±0.005 ANGULAR ±0.5°	
OUTSIDE:		DIMENSIONS ARE SHOWN AS "XXX" REFERENCE DIMENSIONS ARE SHOWN WITH DEC. POINT	
OTHER:		PRODUCT CODE: PROJECT No.	
FILENAME: <input checked="" type="checkbox"/>	FOLDER: <input checked="" type="checkbox"/>		