



PLASTIC/RUBBER SIZES

SIZES SHOWN ARE FOR REFERENCE 3D MODEL IS TO BE USED FOR MANUFACTURING / VERIFICATION		ALL CHANGES MUST BE APPROVED AND RECORDED BY ENGINEERING		
UNIT: INCHES UNLESS DUAL DIMENSION: INCH [METRIC]	PROJECTION 	IPEX Technologies Inc.		
THIS DRAWING AND ALL TECHNICAL INFORMATION APPEARING HEREON ARE PROPERTY OF IPEX TECHNOLOGIES INC. AND MUST BE KEPT IN CONFIDENCE BY THE RECIPIENT. THE SAME MAY NOT BE USED OR REPRODUCED EITHER IN WHOLE OR IN PART WITHOUT THE EXPRESS CONSENT OF IPEX TECHNOLOGIES INC.	TITLE MO40 2 1/2" PVC METER OFFSET SCEPTER		PAPER SIZE ANSI B	SCALE: NA
	PART APPEARANCE:	COLOR:	DRAWN K.D.	DATE 30/03/2021
SURFACE FINISHES: (UNLESS OTHERWISE NOTED)	APP'D	DIMENSIONS ARE IN INCHES TOLERANCES (UNLESS OTHERWISE SPECIFIED)		Critical Dimensions ARE SHOWN AS **x.xx**
INSIDE:		FRACTIONAL	± 1/32	REFERENCE DIMENSIONS ARE SHOWN WITH REF. NOTE
OUTSIDE:		X.X	± 0.015	
OTHER:		X.XXX	± 0.010	
		X.XXX	± 0.005	
FILENAME:	FOLDER:	ANGULAR	± 1.0	PRODUCT CODE: 277084
				PROJECT No.