

# TH404 n/a Track Lighting

12W LED TRACK HEAD ROUND



**Lamp Type** Track Lighting

**Warranty** 3 Year Limited

## Product Specifications

| Item Number | Technology     | UPC                   | Voltage         | Watts         | Incandescent Equivalent | Lamp Shape     | Base                |
|-------------|----------------|-----------------------|-----------------|---------------|-------------------------|----------------|---------------------|
| TH404       | Track Lighting | *                     | n/a             | n/a           | n/a                     | n/a            | n/a                 |
| ANSI Base   | Lamp Code      | Dimmable/Non-Dimmable | Finish          | MOL in inches | MOD in inches           | Initial Lumens | Average Rated Hours |
| n/a         | n/a            | Yes                   | n/a             | n/a           | n/a                     | n/a            | n/a                 |
| Kelvin Temp | Color          | CRI                   | Beam Spread Deg | Pack          | Package Type            | ENERGY STAR    | RoHS Compliant      |
| n/a         | n/a            | n/a                   | n/a             | 12            | Box                     | n/a            | Yes                 |