

S9030 A15 LED

5.5A15/LED/2700K/120V

Lamp Type	LED
Bulb Type	A15
Base Type	E26
Wattage	5.5
Color Temperature	2700
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	450 lumens
Estimated Energy Cost	\$0.60
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	5 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9030	LED	*20045923090305	120	5.5	40	A15	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	5.5A15/LED/2700K/120V	Yes	White	3 15/32	1 7/8	450	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	230	24	Box	Yes	Yes