## SATCO NUVO

## S8916 A19 LED 8.5A19/LED/40K /120-277V

Lamp Type	LED			
Bulb Type	A19			
Base Type	E26			
Wattage	8.5			
Color Temperature	4000			
Color Rendering Index CRI	80			
Warranty	3 Year Limited			



## Lighting Facts Per Bulb

Brightness	800 lumens
Estimated Energy Cost	\$0.96
per year, based on 3 hrs Energy cost depends or use.	
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	e
Warm	Cool 4000 K
Energy Used	8 watts

## **Product Specifications**

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S8916	LED	*20045923089163	120-277	8.5	60	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	8.5A19/LED/40K /120-277V	n/a	White	4 3/16	2 3/8	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	80	220	24	Box	n/a	Yes

Copyright © 2016 Satco Products, Inc. All Rights Reserved. Specifications subject to change Satco Products Inc. 110 Heartland Blvd., Brentwood, NY 11717 1-800-437-2826 • Fax 631-243-2027 www.satco.com