

\$8640 MR16 LED 8MR16/LED/40'/27K/90CRI/12V

Lamp Type	LED
Bulb Type	MR16
Base Type	GU5.3
Wattage	8
Color Temperature	2700
Color Rendering Index CRI	90+
Warranty	3 Year Limited



Lighting Facts Per Bulb

Prightness	490 lumens			
Estimated Energy Cost	\$0.96			
per year, based on 3 hrs Energy cost depends on use.	**			
Average Life	22.8 years			
Based on 3 hrs/day				
Light Appearanc	е			
Warm	Cool			
2700 K				
Energy Used	8 watts			

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S8640	LED	*20045923086407	12	8	75	MR16	GU5.3
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
GU5.3	8MR16/LED/40'/2	7K/90C Re \$2V	n/a	1 7/8	2	490	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	90+	40	48	Box	Yes	Yes