

S9924 T8 LED 43T8/LED/96-840/BP/R17D HO

| Lamp Type | LED |
|---------------------------|----------------|
| Bulb Type | Т8 |
| Base Type | R17d |
| Wattage | 43 |
| Color Temperature | 4000 |
| Color Rendering Index CRI | 82 |
| Warranty | 5 Year Limited |



Lighting Facts Per Bulb

| Brightness | 5500 lumens | | | | |
|--|-------------|--|--|--|--|
| Estimated Energy Cost | \$5.18 | | | | |
| per year, based on 3 hrs Energy cost depends or use. | • | | | | |
| Average Life | 45.7 years | | | | |
| Based on 3 hrs/day | | | | | |
| Light Appearance | ce | | | | |
| Warm | Cool | | | | |
| 4000 K | | | | | |
| Energy Used | 43 watts | | | | |

Product Specifications

| Item Number | Technology | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base |
|-------------|-----------------------------|-------------------|--------------------|---------------|----------------------------|----------------|--------------------------------------|
| S9924 | LED | * | 120-277 | 43 | n/a | T8 | Recessed Double Contact HO/VHO |
| | _ | Dimmable/Non- | _ | _ | _ | _ | Average Rated |
| ANSI Base | Lamp Code | Dimmable Dimmable | Finish | MOL in inches | MOD in inches | Initial Lumens | Hours |
| R17d | 43T8/LED/96- 840/BP/R17d | n/a | n/a | 96 | 1 | 5500 | 50000 |
| | | | | | | | |
| Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant |
| 4000 | Cool White | 82 | 210 | 10 | Egg crate | n/a | Yes |