

# S9942 T8 LED

## 43T8/LED/96-865/BP/R17D HO

Lamp Type	LED
Bulb Type	T8
Base Type	R17d
Wattage	43
Color Temperature	6500
Color Rendering Index CRI	82
Warranty	5 Year Limited



### Lighting Facts Per Bulb

**Brightness** 5500 lumens

**Estimated Energy Cost** \$5.18

per year, based on 3 hrs/day, 11c/kWh.  
Energy cost depends on utility rates and light use.

**Average Life** 45.7 years

Based on 3 hrs/day

#### Light Appearance



6500  
K

**Energy Used** 43 watts

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9942	LED	*	120-277	43	n/a	T8	Recessed Double Contact HO/VHO
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
R17d	43T8/LED/96-865/BP/R17d	n/a	n/a	96	1	5500	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
6500	Daylight	82	210	10	Egg crate	n/a	Yes