

S28766 A19 LED

11.5A19/LED/30K/ND/120V

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	11.5
Color Temperature	3000
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	1100 lumens
Estimated Energy Cost	\$1.32
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	13.7 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	11 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S28766	LED	*20045923287668	120	11.5	75	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	11.5A19/LED/30K/ND/120V	a	n/a	4 3/8	2 3/8	1100	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes