

# S28769 A19 LED

## 11.5A19/LED/27K/ND/120V/4PK

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	11.5
Color Temperature	2700
Color Rendering Index CRI	80
Warranty	3 Year Limited



### Lighting Facts Per Bulb

<b>Brightness</b>	<b>1100 lumens</b>
<b>Estimated Energy Cost</b>	<b>\$1.32</b>
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
<b>Average Life</b>	<b>13.7 years</b>
Based on 3 hrs/day	
<b>Light Appearance</b>	
<b>Energy Used</b>	<b>11 watts</b>

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S28769	LED	*	120	11.5	75	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	11.5A19/LED/27K/ND/120V/4PK	Non-Dimmable	n/a	4 3/8	2 3/8	1100	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	220	12	Box	Yes	Yes