

\$28786 A19 LED 15.5A19/LED/30K/ND/120V

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	15.5
Color Temperature	3000
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	1600 lumens			
Estimated Energy Cost	\$1.81			
per year, based on 3 h Energy cost depends o use.	• .			
Average Life	13.7 years			
Based on 3 hrs/day				
Light Appearan	ce			
Warm	Cool			
3000 K				
Energy Used	15 watts			

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S28786	LED	*20045923287866	120	15.5	100	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	15.5A19/LED/30h	K/ND/120 1/ a	n/a	4 5/8	2 3/8	1600	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes