

## \$28788 A19 LED 15.5A19/LED/50K/ND/120V

Lamp Type	LED		
Bulb Type	A19		
Base Type	E26		
Wattage	15.5		
Color Temperature	5000		
Color Rendering Index CRI	80		
Warranty	3 Year Limited		



## Lighting Facts Per Bulb

Brightness	1600 lumens
Estimated Energy Cost	\$1.81
per year, based on 3 hr Energy cost depends o use.	•
Average Life	13.7 years
Based on 3 hrs/day	
Light Appearance	ce
Warm	Cool
	5000 K
Energy Used	15 watts

## **Product Specifications**

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S28788	LED	*20045923287880	120	15.5	100	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	15.5A19/LED/50h	K/ND/120 <b>1/</b> a	n/a	4 5/8	2 3/8	1600	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	80	220	24	Box	n/a	Yes