

# S29834 A19 LED


## 6A19/OMNI/220/LED/50K

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	6
Color Temperature	5000
Color Rendering Index CRI	80
Warranty	3 Year Limited



### Lighting Facts Per Bulb

**Brightness** 480 lumens


**Estimated Energy Cost** \$0.72 

per year, based on 3 hrs/day, 11c/kWh.  
Energy cost depends on utility rates and light use.

**Average Life** 22.8 years

Based on 3 hrs/day

### Light Appearance



**Energy Used** 6 watts

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29834	LED	*20045923298343	120	6	40	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	6A19/OMNI/220/LED/50K	Yes	n/a	4 3/16	2 3/8	480	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	80	220	24	Box	Yes	Yes