

\$29836 A19 LED 9.8A19/OMNI/220/LED/30K

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	9.8
Color Temperature	3000
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Drinbtness	000 kumana			
Brightness	800 lumens			
Estimated Energy Cost	\$1.08 =			
per year, based on 3 hrs. Energy cost depends on use.	•			
Average Life	22.8 years			
Based on 3 hrs/day				
Light Appearance	e			
Warm	Cool			
3000 K				
Energy Used	9 watts			

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29836	LED	*20045923298367	120	9.8	60	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	9.8A19/OMNI/220)/LED/3 0 %es	n/a	4 3/16	2 3/8	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes