

\$29839 A19 LED 9.8A19/OMNI/220/LED/50K

Lamp Type	LED		
Bulb Type	A19		
Base Type	E26		
Wattage	9.8		
Color Temperature	5000		
Color Rendering Index CRI	80		
Warranty	3 Year Limited		



Lighting Facts Per Bulb

Brightness	800 lumens
Estimated Energy Cost	\$1.08 <u>@</u>
per year, based on 3 hrs/d Energy cost depends on u use.	•
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	
Warm	Cool
	5000 K
Energy Used	9 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29839	LED	*20045923298398	120	9.8	60	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	9.8A19/OMNI/220)/LED/5 0 /es	n/a	4 3/16	2 3/8	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	80	220	24	Box	Yes	Yes