

\$8737 A21 LED 20WA21/LED/HID/27K/120-277V

Warranty	3 Year Limited		
Color Rendering Index CRI	80		
Color Temperature	2700		
Wattage	20		
Base Type	E26		
Bulb Type	A21		
Lamp Type	LED		



Lighting Facts Per Bulb

Brightness	2900 lumens
Estimated Energy Cost	\$2.41
per year, based on 3 hr Energy cost depends o use.	**
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	ce
Warm	Cool
2700 K	
Energy Used	20 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S8737	LED	*20045923087374	120-277	20	n/a	A21	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	20WA21/LED/HID 277V/E26	D/2700K/120- n/a	n/a	5	2 5/8	2900	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	280	24	Box	n/a	Yes