

S29673 n/a LED

45W/LED/HID/40K/100-277V/EX39

Lamp Type	LED
Base Type	EX39
Wattage	45
Color Temperature	4000



IMAGE NOT AVAILABLE

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29673	LED	*	100-277	45	300	n/a	Mogul Extended
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
EX39	45W/LED/HID/4000K/100-277V/EX39	n/a	n/a	n/a	n/a	n/a	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	n/a	300	12	n/a	n/a	Yes