

S29676 n/a LED

100W/LED/HID/40K/100-277V/EX39

Lamp Type	LED
Base Type	EX39
Wattage	100
Color Temperature	4000



IMAGE NOT AVAILABLE

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29676	LED	*	100-277	100	500	n/a	Mogul Extended
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
EX39	100W/LED/HID/4000K/100-277V/EX39	n/a	n/a	9 19/32	5 7/8	n/a	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	n/a	300	4	n/a	n/a	Yes