

S29769 n/a LED

75W/LED/HID/MB/5000K/100-277V

Lamp Type	LED
Base Type	EX39
Wattage	75
Color Temperature	5000



IMAGE NOT AVAILABLE

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29769	LED	*20045923297698	100-277	75	750	n/a	Mogul Extended
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
EX39	75W/LED/HID/MB/5000K/100-277V/EX39	n/a	n/a	n/a	n/a	n/a	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	n/a	360	12	n/a	n/a	Yes