SATCO NUVO

S29910 T5 LED 25T5/LED/46-840/DR

Lamp Type	LED	
Bulb Type	Т5	
Base Type	G5	
Wattage	25	SSATE STATE DA STATE
Color Temperature	4000	
Color Rendering Index CRI	82	

SATCO* 2515/LED/46-640/DR Crystele with Hottonic balant 29W 3500LM 522910	CUUUS CLASSIFIED
--	------------------

Lighting Facts Per Bulb

Brightness	3500 lumens
Estimated Energy Cost	\$3.01
per year, based on 3 hi Energy cost depends o use.	
Average Life	45.7 years
Based on 3 hrs/day	
Light Appearan	се
Warm	Cool
	4000 K
Energy Used	25 watts

Product Specifications

	Miniature Bi Pin
ANSI Base Lamp Code Dimmable/Non- Finish MOL in inches MOD in inches Initial Lumens Av Dimmable	Average Rated Hours
G5 25T5/LED/46- 840/DR n/a n/a 48 5/8 3500	50000
Kelvin Temp Color CRI Beam Spread Deg Pack Package Type ENERGY STAR Ro	RoHS Compliant
4000 Cool White 82 185 10 sleeve n/a	Yes

Copyright © 2016 Satco Products, Inc. All Rights Reserved. Specifications subject to change Satco Products Inc.

110 Heartland Blvd., Brentwood, NY 11717 1-800-437-2826 • Fax 631-243-2027 www.satco.com