

# S28939 n/a LED

60W/LED/HID/TEMP/5K/120-277V

Lamp Type	LED
Base Type	NEMA 5-15
Wattage	60
Color Temperature	5000
Color Rendering Index CRI	85
Warranty	5 Year Limited



## Lighting Facts Per Bulb

Brightness	6000 lumens
Estimated Energy Cost	\$7.23
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	45.7 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	60 watts

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S28939	LED	*	120-277	60	n/a	n/a	Plug 3-Prong
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
NEMA 5-15	60W/LED/HID/TEMP/5K/RC/120-277V	n/a	n/a	10 3/4	6 1/4	6000	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	85	300	4	n/a	n/a	Yes