

S28946 n/a LED 100W/LED/HID/TEMP/5K/120-277V

Lamp Type	LED		
Base Type	NEMA 5-15		
Wattage	100		
Color Temperature	5000		
Color Rendering Index CRI	85		
Warranty	5 Year Limited		



Lighting Facts Per Bulb

Brightness	10000 lumens
Estimated Energy Cost	\$12.05
per year, based on 3 Energy cost depends use.	hrs/day, 11c/kWh. on utility rates and light
Average Life	45.7 years
Based on 3 hrs/day	
Light Appeara	nce
Warm	Cool
	5000 K
Energy Used	100 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S28946	LED	*	120-277	100	n/a	n/a	Plug 3-Prong
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
NEMA 5-15	100W/LED/HID/TE 277V	EMP/5K/RC/120- n/a	n/a	12	6 1/4	10000	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	85	300	4	n/a	n/a	Yes