

S8976 n/a LED

100W/LED/5PC/TEMP/STRING/120V

Lamp Type	LED
Base Type	NEMA 5-15
Wattage	100
Color Temperature	5000
Color Rendering Index CRI	85
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	10000 lumens
Estimated Energy Cost	\$12.05
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	45.7 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	100 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S8976	LED	*	120	100	n/a	n/a	Plug 3-Prong
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
NEMA 5-15	100W/LED/5PC/TEMP/STRING/120V	n/a	n/a	6 5/8	4 1/4	10000	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	85	300	1	n/a	n/a	Yes