

S8706 Retrofit LED

25WLED/CDL/6/4K/100-277

Lamp Type	LED
Bulb Type	Retrofit
Base Type	Connector
Wattage	25
Color Temperature	4000
Color Rendering Index CRI	90



Lighting Facts Per Bulb

Brightness 1900 lumens

Estimated Energy Cost \$3.01

per year, based on 3 hrs/day, 11c/kWh.
Energy cost depends on utility rates and light use.

Average Life 45.7 years

Based on 3 hrs/day

Light Appearance



Energy Used 25 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S8706	LED	*	100-277	25	n/a	Retrofit	Connector
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
Connector	25WLED/CDL/6/4K/100-277	n/a	Silver	7 1/2	7 1/2	1900	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	90	n/a	4	n/a	n/a	Yes