

---

## MANUAL CONTROLLERS

7860 | [Pass & Seymour](#)



---

## FEATURES & BENEFITS

### NEMA 3R Enclosure for 7862 & 7863

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

---

## SPECIFICATIONS

### GENERAL INFO

Type: NEMA 3R Enclosure

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

UN SPSC: 39121507

### DIMENSIONS

Depth (US): 1.66"

Height (US): 3.75"

Width (US): 2.31"

### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

