
MANUAL CONTROLLERS

7863R | [Pass & Seymour](#)



FEATURES & BENEFITS

Manual Control Switch 3pole 60amp 600volt in NEMA 3R Enclosure. Slotted opening on enclosures allows for lock-out, tag-out functionality.

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

SPECIFICATIONS

GENERAL INFO

Number Of Poles: 3-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.66"

Height (US): 3.75"

Width (US): 2.31"

TECHNICAL INFORMATION

Amps: 60A

Volts: 600VAC

Volts (AC): 600

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant



