CSB15AC3I

Llegrand[®] designed to be better.

Hard Use Specification Grade Switch, Ivory

CSB15AC3I



Construction 3way Switch, Back & Side Wire, 15amp 120/277volt, Ivory.



• One-piece brass alloy contact arm for reliable electrical performance.

- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon.

features & benefits

- Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.

specifications

General Info

Color: Ivory Duty: Hard Use Number Of Poles: 3-way

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111 CSA Standard: Yes Federal Spec: Yes Fed Spec Number: WS896 UL Listing No: 20 UL Standard: Yes UN SPS C: 39121507

Dimensions

Depth U S: 1.073" Height U S: 3.281" Width U S: 1.320"

Technical Information

Amps: 15 Amp Volts: 120/277VAC Volts A C: 120/277 Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant