

# Commerical Specification Grade Switch, Brown

CS15AC3



Commercial 3way Switch, Side Wire, 15amp 120/277volt, Brown.



## features & benefits

- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life
- Tri-drive terminal and mounting screws.

specifications

### **General Info**

Color: Brown Type: Side Wire Duty: Heavy Duty

Number Of Poles: 3-way

## **Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 111

CSA Standard: Yes Federal Spec: Yes

Fed Spec Number: WS896

UL Listing No: 20 UL Standard: Yes UN SPS C: 39121507

#### **Dimensions**

Depth U S: 1.073" Height U S: 3.281" Width U S: 1.320"

### **Technical Information**

Amps: 15 Amp Volts: 120/277VAC Volts A C: 120/277

Grade Type: Commercial

## **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant