

Tamper-Resistant Hospital Grade Receptacles, Back & Side Wire, 15A, 125V, Ivory

TR62HI



Tamper-Resistant Hospital Grade Duplex Receptacle Back & Side Wire 15amp 125volt Ivory



features & benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: ivory
Type: Receptacles

Special Features: Tamper-Resistant,back, side wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: UL498

UL Standard: Yes

UN SPS C: 39121406

UR: No

Dimensions

Depth U S: 0.9"

Height U S: 3.281"

Width U S: 1.625"

Technical Information

Amps: 15 Amp

Volts: 125V

Volts A C: 125

Capacity: Duplex

Grade Type: Hospital

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant