

Manual Controller

PS30AC2HP



Double Pole, Single Phase Switch, Back and Side Wire, HP Rated. 30 amps, 277 volts.

features & benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.



specifications

General Info

Number Of Poles: 2

Listing Agencies/Third Party Information

UN SPS C: 39121507

Dimensions

Depth U S: 1.073"

Height U S: 3.281"

Width U S: 1.320"

Technical Information

Amps: 20 Amp
Volts: 277VAC
Volts A C: 277

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant