

Magnetic Latching Relay, 24V/24VDC Control

1070B



Low Voltage Component, Magnetic Latching Relay, 24V/24VDC Control. Reliable field-tested switching circuitry that provide central or local control of lighting loads.



features & benefits

- **Mount** in standard 1/2" KO through noise suppressing nylon ring.
- **Maximum ambient temp:** 140°F (60°).
- **Insulated flame retardant** nylon shell.
- **Prestripped** 5-1/2" (140mm) #22 AWG leads for easy wiring.
- **Split coil design** energizes ON coil to close line contacts, and OFF coil to open contacts.
- **Can be mounted in any position.**
- **Operates** on momentary impulse.
- **Draws** .520 mA.

specifications

General Info

Type: Magnetic Latching Relay

Listing Agencies/Third Party Information

CSA Listing Info: 347V

CSA Standard: Yes

UL Standard: Yes

Dimensions

Diameter U S: 1.176"

Length U S: 3.156"

Technical Information

Volts: 24V

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant