



POWER OUTLET RECEPTACLE OPENINGS, ONE GANG, BROWN

TP720 | [Pass & Seymour](#)

FEATURES & BENEFITS

One Gang Power Outlet Receptacle Opening, 1.5938" hole for 1.5625" diameter device - 2 mtg. holes, Brown Nylon.



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

SPECIFICATIONS

GENERAL INFO

Color: Brown
Size: Standard
Special Features: Unbreakable

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121704
UR: No

DIMENSIONS

Diameter (US): 1.5938" Hole

TECHNICAL INFORMATION

Material: Nylon

Capacity: 1-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

