# TradeMaster Receptacle

32321



Duplex Grounding Receptacle with high-impact resistant thermoplastic construction. It has ultrasonic welding of face to back body and long-term blade retention. 15 amp, 125 volt. Ivory.

## features & benefits

- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping. Extra-large circuit break-off tabs.
- Side-access push wire release. Side wire accepts #12 #14 AWG solid wire. Push wire accepts #14 AWG solid only.
- Low profile face. Traditional contoured face. (3232 models) Self-grounding models provide automatic ground clip.

## specifications

#### **General Info**

Color: Ivory Number Of Poles: 2 Number Of Wires: 3

#### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42 CSA Standard: Yes Federal Spec: No UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406

Dimensions

3232I

Depth U S: 0.96" Height U S: 3.31" Width U S: 1.32"

#### **Technical Information**

Amps: 15 Volts: 125 Volts A C: 125

### **Buy American Act Compliance**

Country of Origin: CHINA Buy American Act Status: No