

# 30 Amp Non-NEMA Connector - Black Back, White Front Body

3433SS



Connector 4wire 30amp 120/208volt  
Turnlok



## features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## specifications

### General Info

Color: Black, White  
Type: Connector

Number Of Wires: 4  
Special Features: Non-Nema

**Listing Agencies/Third Party Information**

Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: 498  
UL Standard: Yes  
UN SPS C: 39121403

**Dimensions**

Diameter U S: 2.20"  
Length U S: 3.33"

**Technical Information**

Amps: 30 Amp  
Volts: 120/280V  
Volts A C: 120/280

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant