

---

## 15 AMP NEMA L515 FLANGED OUTLET, GRAY

4715SS | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

#### Turnlok Flanged Outlet 3wire 15amp 125volt Grounding

- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Type: Flanged Inlet  
Number Of Wires: 3  
Special Features: Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403

#### DIMENSIONS

Depth (US): 1.374"  
Diameter (US): 2.562"

#### TECHNICAL INFORMATION

Amps: 15A  
NEMA Configuration Number: L515  
Volts: 125V  
Volts (AC): 125

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

