

Hospital Grade Quad Receptacles

420HRED



Hospital Grade Quad Receptacle 20amp
125volt Red

features & benefits

- Rugged nylon face and body withstands impacts and hard use.
- Built-in wire stripping gauge.
- Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
- Heavy-duty, phosphor bronze contacts.
- Shielding walls guard against live-circuit-to-ground shorts.
- Split circuit break-off tabs.
- UL and CSA listed.



specifications

General Info

Color: Red
Type: Quad, Receptacles
Special Features: Split Circuit

Listing Agencies/Third Party Information

CSA Standard: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Height U S: 4.5"
Width U S: 4.5"

Technical Information

Amps: 20
Volts: 125V
Volts A C: 125
Capacity: Quad
Grade Type: Hospital

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant