legrand^{*} designed to be better.

Heavy-Duty Spec Grade Single Receptacle, Side Wire, 15A, 125V, White

5251W

Heavy-Duty Spec Grade Single Receptacle, Side Wire 15amp 125volt, Ivory



features & benefits

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screwpressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wire power contacts for lasting retention.

specifications

General Info

Color: white Type: Single,Receptacles Duty: Heavy Duty Special Features: Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42 CSA Standard: Yes Federal Spec: No UL Listing No: UL498 UL Standard: Yes 5251W

UN SPS C: 39121406 UR: No

Dimensions

Depth U S: 1.08" Height U S: 3.28" Width U S: 1.32"

Technical Information

Amps: 15 Amp Volts: 125V Volts A C: 125 Capacity: Single Grade Type: Federal Specification

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant