



## HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 15A, 125V, LIGHT ALMOND

5261LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

Heavy-Duty Spec Grade Single Receptacle Back & Side Wire 15amp 125volt Light Almond



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Single Receptacles  
Duty: Heavy Duty  
Special Features: Back,Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
cURus: No

Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### **DIMENSIONS**

Depth (US): 1.093"  
Height (US): 3.28"  
Width (US): 1.32"

#### **TECHNICAL INFORMATION**

Amps: 15A  
Volts: 125V  
Volts (AC): 125  
Capacity: Single  
Grade Type: Federal Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

