Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Brown

5362A

Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Brown





# features & benefits

- One-piece brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.
- Auto-ground clip assures positive ground.
- Corrosion-resistant models have nickel-plated straps and contacts.

# specifications

Color: brown Type: Receptacles Duty: Extra Heavy Duty

Special Features: Back, Side Wire

## **Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes Federal Spec: Yes

Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406

UR: No

#### **Dimensions**

Depth U S: .900" Height U S: 3.281" Width U S: 1.625"

#### **Technical Information**

Amps: 20 Amp Volts: 125V Volts A C: 125 Capacity: Duplex Grade Type: Industrial

### **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant