



SHORT STRAP SPEC GRADE SINGLE RECEPTACLE, SIDE WIRE, 20A, 125V, BROWN

5358 | [Pass & Seymour](#)

FEATURES & BENEFITS

Short Strap Spec Grade Single Receptacle, Side Wire, 20amp 125volt, Brown



- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tri-drive steel terminal screws.
- One-piece brass triple-wipe power contacts for lasting retention.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Typical Applications: Short Strap

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No.42
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 1.00"
Height (US): 1.75"

Width (US): 1.49"

TECHNICAL INFORMATION

Amps: 20A

Volts (AC): 125

Capacity: Single

Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

