legrand[®] designed to be better.

Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Brown



5362

Hard Use Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Brown



features & benefits

- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 #14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: brown Type: Receptacles Special Features: Back, Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42

5362

CSA Standard: Yes Federal Spec: Yes Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406 UR: No

Dimensions

Depth U S: .780" Height U S: 3.281" Width U S: 1.322"

Technical Information

Amps: 20 Amp Volts: 125V Volts A C: 125 Capacity: Duplex Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant