

Heavy-Duty Spec Grade Single Receptacles, Side Wire Right Angle Slots, 20A, 125V, Ivory

5371I



Heavy-Duty Spec Grade Single Receptacle,
Side Wire Right Angle Slots, 20amp
125volt, Ivory.



features & benefits

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tri-drive steel terminal screws.
- One-piece brass triple-wipe power contacts for lasting retention.

specifications

General Info

Color: ivory
Type: Single,Receptacles
Duty: Heavy Duty
Special Features: Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: 0.95"

Height U S: 3.28"

Width U S: 1.32"

Technical Information

Amps: 20 Amp

Volts: 125V

Volts A C: 125

Capacity: Single

Grade Type: Federal Specification

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant