

# Heavy-Duty Spec Grade Single Receptacles, Side Wire Right Angle Slots, 20A, 125V, White

5371W



Heavy-Duty Spec Grade Single Receptacle,  
Side Wire Right Angle Slots, 20amp  
125volt, White.



## features & benefits

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tri-drive steel terminal screws.
- One-piece brass triple-wipe power contacts for lasting retention.

## specifications

### General Info

Color: white  
Type: Single,Receptacles  
Duty: Heavy Duty  
Special Features: Side Wire

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406  
UR: No

**Dimensions**

Depth U S: 0.95"

Height U S: 3.28"

Width U S: 1.32"

**Technical Information**

Amps: 20 Amp

Volts: 125V

Volts A C: 125

Capacity: Single

Grade Type: Federal Specification

**Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant