

# Heavy-Duty Spec Grade Single Receptacles, Back & Side Wire, 15A, 250V, Brown

5671



Heavy-Duty Spec Grade Single Receptacle  
Back & Side Wire 15amp 250volt Brown



## features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

## specifications

### General Info

Color: brown  
Type: Single,Receptacles  
Duty: Heavy Duty  
Special Features: Back,Side Wire

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42  
CSA Standard: Yes

Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406  
UR: No

**Dimensions**

Depth U S: 1.093"  
Height U S: 3.28"  
Width U S: 1.32"

**Technical Information**

Amps: 15 Amp  
Volts: 250V  
Volts A C: 250  
Capacity: Single  
Grade Type: Federal Specification

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant