

Heavy-Duty
Spec Grade
Single
Receptacles,
Back & Side
Wire, 20A, 250V,
White

5871W

Heavy-Duty Spec Grade Single Receptacle Back & Side Wire 20amp 250volt White





## features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

# specifications

## **General Info**

Color: white

Type: Single, Receptacles

**Duty: Heavy Duty** 

Special Features: Back, Side Wire

#### **Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

cURus: No

Federal Spec: Yes

Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406

UR: No

#### **Dimensions**

Depth U S: 1.093" Height U S: 3.28" Width U S: 1.32"

#### **Technical Information**

Amps: 20 Amp Volts: 250V Volts A C: 250 Capacity: Single

Grade Type: Federal Specification

## **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant