

# Toggle Switch Openings, One Gang, 430 Stainless Steel

SL1



Smooth Metal Wall Plate 1gang Toggle 430 Stainless Steel





- Type 430 Stainless Steel, magnetic: .032" nominal thickness.
- Brushed finish.

features & benefits

- Less corrosion-resistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and industrial buildings.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## specifications

#### **General Info**

Size: Standard Type: Toggle

#### **Listing Agencies/Third Party Information**

CSA Listing Info: Yes CUL Listing No: No

cULus: No

cURus: No Federal Spec: No UL Listing No: Yes UN SPS C: 39121704

UR: No

#### **Dimensions**

Weight: 0.12684

#### **Technical Information**

Material: 430 Stainless Steel

Capacity: 1-gang

### **Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA Buy American Act Status: Buy American Act Compliant