

Clock Hanger Receptacles, Recessed with Smooth Wall Plate, 15A, 125V, Ivory

S3713I



Clock Hanger Recessed Receptacle with
Smooth Wall Plate 15amp 125volt Ivory

features & benefits

- Single recessed receptacle.
- Smooth wall plate.



specifications

General Info

Color: Ivory
Type: Clock Hanger
Special Features: Clock Hanger
Style: Decorator, Smooth

Listing Agencies/Third Party Information

CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: 1.878"
Height U S: 4.478"
Width U S: 2.74"

Technical Information

Amps: 15 Amp
Volts: 125V
Volts A C: 125
Grade Type: specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant