

# Non-Grounding Combination Switches

690W



Single Pole, Double Switch, 15 amps, 120/277 volts, White.

# features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.



## specifications

#### **General Info**

Type: Combination, Double Number Of Poles: 1

Special Features: Non-Grounding

#### **Listing Agencies/Third Party Information**

UL Listing No: 20 UL Standard: Yes UN SPS C: 39121406

#### **Dimensions**

Depth U S: 0.94" Height U S: 3.28" Width U S: 1.32"

#### **Technical Information**

Amps: 15 Amp Volts: 120/277VAC Volts A C: 120/277

### **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant