

Non-NEMA 3-Wire Single Receptacle

7310



Turnlok Receptacle 3pole 3wire 20amp
125/250v



features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

specifications

General Info

Type: Single, Receptacles
Number Of Wires: 3
Special Features: Non-Nema

Listing Agencies/Third Party Information

UN SPS C: 39121403

Technical Information

Amps: 20 Amp
Volts: 125/250V
Volts A C: 125/250

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant